

Easier application with wider range
REUSABLE RECESS FORMERS FOR
HALFEN HCC COLUMN SHOES: HCC16 - HCC39

NEW



Main features at a glance:



> Sustainable and environment-friendly



> Easy to install and remove



> Time saving, efficient installation

THE NEW HALFEN HCC RECESS FORMERS

› fast › simple › colour-coded sizes



QUICK INSTALLATION

The new HALFEN HCC Recess formers with fixing bolts allow quick and exact installation of HALFEN HCC Column shoes to the formwork. No need for adhesives to fix the recess formers to the formwork, therefore making the entire installation more efficient and faster.




Assembly instructions are available for download at www.halfen.com

EASY REMOVAL OF FORMWORK

The new HCC Recess formers are very robust and therefore reusable. Removing the formwork: The fixing bolt, which has already been used for installation, is screwed into the hole in the side of the recess former and used as a lever for removal.

This process is non-destructive: however, it is essential to lubricate the recess formers sufficiently with formwork grease before pouring the concrete to avoid possible damage and maximize service life.



CLEARLY DEFINED COLOUR CODED SIZES

The new HCC Recess formers are made of polyurethane, suitable for use in edges and corners.

The HCC Recess formers are available in 5 sizes as standard: Each size is assigned a specific colour. This colour coding provides better overview of the sizes and minimises the risk of mix-ups.

Leviat

Please contact Leviat for more information on these products. Full contact details are available online at Leviat.com.

info@leviat.com

Imagine. Model. Make.

Leviat.com